

TORQUE WRENCHES WITH REVERSIBLE RATCHET

810 N

ISO 6789



- Adjustable torque model for clockwise tightening
- Accuracy $\pm 4\%$ of the preset torque value
- Readings in Nm
- Sensible and audible alarm on reaching preset torque value
- Automatic resetting on pressure release after disengagement
- Supplied with test certificate

Family details

Code	Capacity Nm	Resolution Nm	■ Male square drive "	L mm	Quantity for packaging
U08104000	1÷5	0,05	1/4	197	1
U08104001	5÷25	0,05	1/4	290	1
U08104002	10÷50	0,25	3/8	350	1
U08104003	20÷100	0,25	1/2	410	1
U08104005	40÷200	0,5	1/2	475	1
U08104006	68÷340	1	1/2	630	1

Sets / Compositons

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000

Articles



496 E4 - Assortment for industrial maintenance (256 pcs.)



496 E7 - Assortment for industrial maintenance (209 pcs.)

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo
da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000