



Needle roller bearings RNA4905-2RSR-XL (Series RNA49..-2RSR)

dimension series 49, lip seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	30 mm	
D	42 mm	
C	17 mm	
rmin	0,3 mm	
m	60 g	Mass
Cr	21800 N	Basic dynamic load rating, radial
C0r	24200 N	Basic static load rating, radial
Cur	4650 N	Fatigue limit load, radial
nG Fett	8600 1/min	Limiting speed for grease lubrication

