



Specifications:

Contact rating: 500mA, 30V DC
 Contact resistance: 100mOhm max.
 Insulation resistance: 100MOhm min. at 500V DC
 Dielectric strength: 250V AC for 1 minute
 Operating temperature: -20°C to +70°C
 Mechanical life: 300 000 cycles min.
 Operating force: 50gf max.
 Soldering conditions: 260 +/-5°C, 3sec. max.
 Material: Cover / plunger: POM, UL94HB
 Body / lever: PBT, UL94V-0
 Contact: BeCu with silver plated
 Terminals: brass, silver plated

Compliance: RohS II (2011/65/EU)

Tolerances:0.00 to 30.00:±0.20mm 30.01 to 80.00:±0.25mm	Date	Name
	11/05	dr
Travel	08/14	dr
Rename	07/13	dr
Material	12/12	dr
Revised	03/10	dr
Modifications	Date	Name

DM-SSM-01C-L2

knitter-switch

30 07 27

Page

1/1