

ME MAX 22,5 3-3 KMGY

Order No.: 2713939

The illustration shows the housing versions



Electronic housing consisting of: Housing shells left and right, front plate, transparent cover, metal foot catch and spring, open housing, 24-pos. (6 x 4 pos.), width: 22,5 mm, color: Light gray

Commercial data	
GTIN (EAN)	4 017918 936259
sales group	F052
Pack	10 pcs.
Customs tariff	85472000
Catalog page information	Page 620 (CC-2011)

Product notes WEEE/RoHS-compliant since: 04/01/2005



http://

www.download.phoenixcontact.com Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Housing type	Complete housing
Housing material	Polyamide
Color	light gray

Dimensions / positions

Length	99 mm
Constructional height	114.5 mm
Width	22.5 mm
Number of positions	24

Technical data

Ambient temperature (operation)	-40 °C 105 °C
Inflammability class acc. to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	6.1 W 12.1 W

Certificates / Approvals



Certification CUL, UL

Accessories


Item Designation Description

Plug/Adapter


2908294 ME FE-CONTACT Functional earth ground contact, for intermediate elements.

Diagrams/Drawings

Dimensioned drawing



Dimensional drawing of the ME MAX 3-3 printed circuit board, for printed circuit terminal block connection (MKDSO), view: component side



Dimensional drawing of the ME MAX 3-3 printed circuit board for plug connection (MSTBO), view: component side

