




6	61 03 000 0044	Cable clamp metal hood 9-37P dia.7-10mm	1
5	09 67 000 7570	DSUB MA turned contact_AWG 24-28_PL1 HMC	8
4	09 14 008 3034	Han Gigabit Cat8, male	1
3	09 15 200 6222	Han D F crimp contact 1,0 mm ² Au/HMC	16
2	09 58 024 3101	UICIT_8/16_I_HMC_FI_CRT_0,09-1,5mm ²	1
1	09 58 001 0313	UICIT_H_WMRF_RAL1003	1
Si. no	Part number	Part Name	Qty

Note:
1. Dimensions are in mm and only for reference purpose only.
2. Refer data sheet for product specification.

	All Dimensions in mm Original Size DIN A2		Scale 1:1	Free size tol.		Ref. Sub.	
	All rights reserved		Created by 404742	Inspected by 402933	Standardisation	Date 06-Nov-2024	State 40 - Released
	Department EL PD		Title UICIT_WMRF 8/16_KIT				Doc-Key / ECM-Nr. DS00235602
	HARTING D-32339 Espelkamp		Type TB	Design Number DS00235602	SAP Mat. Number 09580241032		Rev. B Page 1/1