

**TSHE60-XL-N**

Plummer block housing unit

Plummer block housing units TSHE, cast iron housing, radial insert ball bearing with eccentric locking collar, T seals

X-life

Technical information



Your current product variant

Groove	N	Cast iron housing with undercut slot for end caps
Material	GG	Grey cast iron

Main Dimensions & Performance Data

d	60 mm	Bore diameter
L	150 mm	Length total
H 2	140 mm	Height
≈m	4.21 kg	Weight

Mounting dimensions

J	118 mm	Distance fixing bore
K	M16	Thread fixing bore

Dimensions

H	69.9 mm	Distance shaft axis
A	60 mm	Width (base)
A 1	42 mm	Width (head)
Q	M6	Connection thread for lubrication
B 1	77.9 mm	Locking collar total width
S 1	46.9 mm	Distance of raceway to locking collar



Additional information

SHE12	Housing
GE60-XL-KTT-B	Bearing designation
KASK12	Protecting cap

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.