



Datasheet


RS PRO M12 Male Rear Panel Mount 4 Pin D-Coded Connector

Part No: 2017219



Technical Specifications:

Rated Operational Voltage	250 V
Current Rating	4 A
Insulation Resistance	≥100 MΩ
Temperature Range	-25° +85°C
Coding	D-Coded
Degree of Protection	IP67
Mounting	Rear,M16x1.5 thread
Housing Material	Brass Ni Plated
Contact	Cu-Zn
Contact Plating	Gold Flash
Contact Carrier	Nylon 66
O-ring	Neoprene
Clamp Nut	M16 x 1.5



Quality Standard: IEC 61076-2-101



Type Approved Safety Regular Production Surveillance







