



# CSB P W 190 x 30 x 2,1 x 48ATB

## CIRCULAR SAW BLADES FOR HAND HELD CIRCULAR SAWS

- PTFE coating: Cuts cooler, non stick for quicker cuts. Protects against corrosion and accumulation of resin.
- Laser cut vibration slots: Low vibration and increased accuracy. Slots are filled with polyurethane and act as shock absorbers by isolating the teeth from vibration.
- High grade laser cut steel: Guaranteed accuracy.
- Premium cobalt infused tungsten carbide: Sharp and clean cuts.
- \*Thin Kerf: Cordless optimised, extra thin cutting width for maximum runtime
- \*All wood types: Soft/ hardwood, plywood, laminated chipboard, melamine, MDF
- \*\*Standard blades without PTFE coating and vibration slots



All Wood Types	✓
Article Number	4932471380
Blade diameter (mm)	190
Bore size (mm)	30
Clean Cut	✓
Cutting width (kerf) (mm)	2.1
Hook Angle	+10°
No. of teeth	48
Pack quantity	1
Thin Kerf	✓
Tooth Form	ATB