



PRODUCT-DETAILS

SS32/25M**32MM GS CONDUIT 25M - MET****General Information**

Extended Product Type:	SS32/25M
Product ID:	7TCA296120R0032
EAN:	5020963005947
Catalog Description:	32MM GS CONDUIT 25M - MET
Long Description:	Inherent Low Fire Hazard Conduit, 1 Inch, Nominal Conduit Size 32mm, Outside Diameter 32.0mm, Inside Diameter 28.1mm, Static Bend Radius 60mm, Reel Length 25 Meters, 316 Stainless Steel, Corrosion Resistant
Display Name:	SS32/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Indoors / Outdoors - Corrosive Environments

Ordering

EAN:	5020963005947
-------------	---------------

UPC: 786210249575

Dimensions

Outside Diameter: 32.0 mm

Technical

Number of Batteries: 0

Material: Stainless Steel

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963005947

Package Level 1 Height: 12 in
305 mm

Package Level 1 Depth / Length: 16 in
406 mm

Package Level 1 Width: 16 in
406 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

