



ENGLISH

Datasheet

Stock No: 299-4109

# RS Pro Pneumatic Elbow Threaded-to-Tube Adapter, R 1/4 Male, Push In 6 mm



## Product Details

Elbow Adaptor - Male Tapered/Parallel

Threaded, Tube-to-Tube & Adaptors

Threaded Tube-to-Tube & Adaptors

The push-on and screw collar design of these fittings makes them secure and suitable for instrumentation, vacuum and general purpose applications, and they can be used with nylon or polyurethane tubing.

Operating Temperature Range -18 to +70°C

Operating Pressure of -1 to 15 bar

## Specifications:

Threaded Connection	R 1/4 Male
Tube Connection	Push In 6 mm
Tube Connection - Tube Size	6mm
Threaded Connection - Thread Size	1/4in
Angle	90°
Threaded Connection - Gender	Male
Manufacturer Series	1100
Tube Connection - Type	Push In
Threaded Connection - Thread Standard	R
Minimum Operating Temperature	-18°C
Maximum Operating Temperature	+70°C
Maximum Operating Pressure	15 bar