



CERTIFICATION RECORD

The company named below has been authorized by CSA to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products, according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

File No: 043989 0 000

Class No: 6221 02 ATTACHMENT PLUGS - Fuseless

SUBMITTOR

Bulgin Components PLC
Bypass Rd. Barking
Essex, IG11 0AZ
ENGLAND
Attention: Mr. Brian Taylor
Manager, Approvals

FACTORY

51896 Bulgin Components PLC
Bypass Rd. Barking
Essex, IG11 0AZ
ENGLAND
Attention: Mr. Brian Taylor
Manager, Approvals

October 9, 1997(Replaces January 10, 1996)

- Motor attachment plugs, 15A, 250V, 2-pole, 3-wire grounding, Types P575, P580, P580/1, Q1950, P579, Q2112/5, P590, P595, P580/PC/7MM, P580/PC/7MM/LC, Q2422/1, Q2422/2.
- Motor attachment plugs (flanged equipment power inlets), 2-pole, 2-wire, Cat Nos. P690/PC, P690/PC/12132, P690/PC/7 and P690/PC/7/LC; 2-pole, 3-wire, Cat Nos. P580/PC/12132; 15A, 250V.
- Motor attachment plugs, 15A, 250V, 2-pole, 2-wire, Type P690, P691.
- Special purpose coupler, 10A, 250V, 2-pole, 3-wire grounding, Type P597.
- Special-use pull-off plug, 2-pole, 3-wire grounding, 10A, 250V, Type P587.
- Special purpose couplers, 2-pole, 2-wire, 15A, 250V Types P705, P725.
- Special purpose couplers, 2-pole, 2-wire, 10A, 250V, Types P715, P772, P782.
- Special purpose couplers, 2-pole, 3-wire grounding, 15A, 250V, Types P675, P695; 10A, 250V, Types P685, P686, P770, P780.

TO THE REQUIREMENTS OF CSA STANDARD C22.2 NO. 182.3-M1987

- Special-use pull-off plug, 2-pole, 3-wire grounding, 10A, 250V, type P587/SE.
- Motor attachment plugs (appliance inlets), Type P.575/PC, 15A, 250V ac. Types BZM.1, BZM.2, 10A, 250V ac, 2-pole, 3-wire grounding.



-
- Motor attachment plugs (appliance inlets), 2 pole, 3 wire grounding, Type P783 and P793, 15A, 250V ac.
 - Motor attachment plugs (appliance inlets), types P784, P785 and P786, rated 2.5A, 250V, 2-pole, 2-wire, non-polarized.
 - Rewireable appliance connectors, 2 pole, 3 wire grounding, Type P686 and P686/SE, 10A, 250V ac.

Notes:

1. The plugs are sold only to manufacturer's for assembly of Certified electrical equipment.
2. Each plug or coupler may have the following suffix added to the type designation, /PC, /TERM, /110, /187, /250 or /28, /48, /63 as appropriate.
3. Couplers may also be marked for panel thickness, 0.5-4.0mm.

CL