

## Han 48HPR cover 4XM40



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 048 9901
Specification	Han 48HPR cover 4XM40
HARTING eCatalogue	<a href="https://harting.com/19400489901">https://harting.com/19400489901</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> HPR
Type of hood/housing	Mounting cover
Description of hood/housing	Distance bolt M5 for female inserts

### Version

Size	48 B
Number of cable entries	4
Cable entry	4x M40
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	4 distance pieces 4x M6 screw 4 washers

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653



**Pushing Performance**  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	500 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140130425
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467