

## **FEATURES**

- EPDM exhibits outstanding resistance to heat, ozone, steam, and weather.
- EPDM liners prevent damage to the surface and vibration
- Pressed step band flush with the surface
- Stainless steel is made from 18/8 stainless steel
- Operating temperature range -40'c-150'c
- REACH & RoHS Complaint

# RS PRO P-Clips Stainless Steel with EPDM Rubber



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.


# P-Clips Steel with EPDM Rubber



#### **Product Description**

RS Pro P-clip is one-piece clip made of 304 Stainless Steel material with EPDM rubber line. The EPDM rubber liner covers from clamp edge which it reduces vibration and provides a tight fit. P-Clip is used to lock cables, hoses, tubes, and pipe in place with one screw or bolt.

### **General Specifications**



RS Stock No.	Description	Ranges Diameter		Nominal	DIAMENSION (mm)				
		mm	inch	Diameter (ØD)	Α	Е	t	Ød.1	d.2
				mm.					
	2538554	19.5-22	49/64 - 55/64	20	12.7	17	0.7	M6 /	8.6
	2538555	20.5-23	13/16 - 29/32	21				6.6	
	2538556	21.5-24	27/32 - 15/16	22					
	2538558	24.5-27	31/32 - 1 1/16	25					
	2538559	26.5-29	1 3/64 - 1 9/64	27					
	2538560	27.5-30	1 5/64 - 1 1/8	28					
	2538561	28.5-31	1 1/8 - 1 7/32	29					
	2538562	29.5-32	1 5/32 - 1 17/64	30					
	2538564	31.5-34	1 15/64 - 1 11/32	32					
	2538565	34.5-37	1 23/64 - 1 29/64	35					
	2538566	39.5-42	1 9/16 - 1 21/32	40					
	2538567	43.5-46	1 23/32 - 1 13/16	44					
	2538568	47.5-50	1 7/8 - 1 31/32	48					
	2538569	51.5-54	2 1/32 - 2 1/8	52					

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories