


Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	Verbatim GmbH			
	Supplier's address.	Support, Duesseldorfer Strasse 13, 65760 Eschborn, DE			
2.	Model identifier	32239Verbatim PMT-17-4K			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	A			
4.	On mode power demand in SDR	18,5			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	A			
6.	On mode power demand in HDR, if implemented	18,5			W
7.	Off mode, power demand, if applicable	1,1			W
8.	Standby mode power demand, if applicable	1,1			W
9.	Networked standby mode power demand, if applicable	n.a.			W
10.	Electronic display category	Monitor			
11.	Size ratio	16	:	9	
12.	Screen resolution	3 840	x	2 160	pixels
13.	Screen diagonal	43,8			cm
14.	Screen diagonal	17			inches
15.	Visible screen area	300,0			dm²
16.	Panel technology used	A-Si TFT Active Matrix			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	60			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	5			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	5			Years
23.	Minimum guaranteed product support	5			Years
	Minimum duration of the general guarantee offered by the supplier	2			Years
24.	Power supply type	External			
25.	External power supply (non standardized and included in the product box)				
	i	USB			
	ii	Input voltage	240		V

	<i>iii</i>	Output voltage	5,0	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

Model placed on the Union market from 29/02/2024



EPREL registration number: 1922303

<https://eprel.ec.europa.eu/qr/1922303>

Supplier: Verbatim GmbH (Manufacturer)

Website: <https://www.verbatim.de/>

Customer care service:

Name: Support

Website: <https://www.verbatim-europe.com>

Email: support@verbatim-europe.com

Phone: 00 800 3883 2222

Address:

Duesseldorfer Strasse 13
65760 Eschborn
Germany