



18 mm 3/8" impact socket STD - 1 pc

SHOCKWAVE™ IMPACT DUTY IMPACT SOCKETS

- SHOCKWAVE™ IMPACT DUTY steel (Chrome-Molybdenum) is high quality alloy steel which provides ultimate strength and durability.
- Best fitting thanks to 6 gripping points.
- Non-slip hex geometry to prevent socket and fastener rounding.
- Deep wall construction provides clearance for protruding bolts.
- Stamped and ink filled diameter markings and laser etched part number for wear resistance.
- Dual hole design and groove for security accessories.



ø (mm)	25.8
Article Number	4932480275
For anchor rod thread size	M12
Pack quantity	1
Size AF [across flats][mm]	18
Tool reception	3/8" square
Total length (mm)	34
Working depth [mm]	10.2
Working length (mm)	10.2