



Main

Range of product	Odace
Product or component type	USB charger
Device application	Charger
Device presentation	Mechanism with fixing frame
Device mounting	Flush
Type of USB power supply	USB type C
Integrated connection type	1 USB type C 5 V DC, maximum load current: 3 A
Condition of use	Indoor

Complementary

Colour tint	Cobalt blue
Output current	3 A
[Ue] rated operational voltage	100...240 V AC +/- 10 % at 50/60 Hz
Power consumption in W	0.1 W
Max output power on one port	65 W
Material	Plastic: housing
Protection type	Short-circuit Surge Overheating Overvoltage Overcurrent
Number of terminals	2 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	2 x 0.75...2 x 2.5 mm ² for rigid cable(s) 2 x 0.75...2 x 2.5 mm ² for flexible cable(s)
Wire stripping length	7 mm
Fixing mode	By screws
Height	71 mm
Width	71 mm
Depth	42 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for operation	0...40 °C
Product certifications	EAC
Electrical insulation class	Class II
IK degree of protection	IK04
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information