



CAPABILITIES AND CUSTOM OPTIONS

KNOW MORE ABOUT PE30 AND P30L SERIES

Features	Advantages
High power rating: 3 W at 70 °C	Can operate under a high working input DC voltage
Long life version available: P30L	Offers a long lifespan > 2 M cycles
Sealing level: IP67	Fully sealed model, perfect for harsh environments
Three different tapers (or electrical laws): A, linear / L, logarithmic / F, inverse clockwise logarithmic	Cover a wider range of applications
Cermet track	Wider ohmic range / lower temperature coefficient

Customization	Series
Shaft locking option: DBAN	PE30LD
Locating PEG	PE30LL / P30LLL
Center detent: CV1M	PE30
Three standard shaft lengths: 16 mm FMF, "FG" / 25 mm FMF, "FL" / 50 mm FMF, "FR"	PE30L / P30LL