

Datasheet

2.41mm Pitch 62 Way Right Angle Through Hole Mount PCB D-sub Connector, Socket

RS Stock number [484-852](#)



Description:

90° PCB Socket

Grounding fingers on the shell for EMI/RFI shielding

Accepts standard 'D' sub miniature accessories

Suitable for military, industrial or commercial applications and computer interfacing etc.

RS, Professionally Approved Products, gives you professional quality parts across all product categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

Specification:

Body Orientation: Right Angle

Contact Material: Copper Alloy

Current Rating: 5A

Depth: 12.55mm

Gender: Female

Housing Material: Nylon

Maximum Operating Temperature: +125°C

Minimum Operating Temperature: -55°C

Mounting Type: Through Hole

Number of Contacts: 62

Pitch: 2.41mm

Voltage Rating: 350 V

Wire Accommodation: 22-32 AWG

Dimensions:

