

AKBU 35 PMQW Select

Cordless universal magnetic core drill for up to
35 mm

Order number:: 7 170 02 62 00 0

FEIN SELECT⁺



Small and powerful single-speed cordless universal magnetic core drill with forward/reverse running, MT2 tool mounting, permanent magnet and maximum functionality for mobile working on the construction site.

- Extremely low-wear tool design with swivel-mounted motor cable protection hose for tough use in industry and manual trades.
- Small and light tool for continuously good work progress thanks to brushless FEIN PowerDrive motor with tacho electronics and FEIN HighPower storage battery with cells with high current capability.
- Flexibility for all mobile drilling work, such as core drilling, twist drilling, tapping, countersinking and reaming.
- FEIN HighPower Li-ion battery. Continually high power output with 75% higher current rating than a Li-ion battery for good work progress.
- Simple operating concept avoids mix-ups and can be clearly seen by the user.
- Convenient magnetic holding force display.
- Tilt sensor.
- Reversible.
- Electronic speed setting.
- Extra large stroke range.
- MT2 tool mounting.
- Extra narrow permanent magnet with magnetic bias.
- Speed saving "memory function".
- The battery charge can be read off the battery.
- FEIN SafetyCell technology. Protects the battery and tool from overload, overheating and total discharge.
- 3-year FEIN PLUS warranty including battery and charger.
- * Also available with accessories.
- ** Maximum performance with FEIN HighPower Li-ion battery



AKBU 35 PMQW Select

Cordless universal magnetic core drill for up to 35 mm

Order number:: 7 170 02 62 00 0

Technical data

Battery voltage	18 V
Motor	brushless
Speed, full load	130 - 520 rpm
Tool Holder	MK 2
Twist drill max. Ø	18 mm
Core drill, drilling depth max.	50(75)* mm
Tapping	M 14
Countersinking max. Ø	31 mm
Reaming max. Ø	18 mm
Carbide core drill bit max. diameter	35 mm
HSS core drill max. Ø	35 mm
Core drill holder	3/4 in Weldon
Changing the core bit	tool-free
Stroke	135 mm
Total stroke range	260 mm
Magnetic holding power	9 000 N
Magnetic foot dimensions	195 x 70 mm
Weight without battery	12,10 kg
Cordless	X

Included in price::

1 x coolant pump
1 lashing strap
1 swarf hook
1 centering pin
1 contact guard
1 drift key
1 case