



## Main

Range	Thorsman
Range of product	PROchantier
Product name	Thorsman cable reel Extended
Product or component type	Extension cable reel
Device application	Power supply
[Ue] rated operational voltage	230 V
[In] rated current	13 A
Colour tint	Green/black

## Complementary

Outlet standard	CEE 7/5
Outlet standard deviation	French
Cable length	25 m
Cable cross section	2.5 mm²
Type of cable	H07RN-F3G2.5
Height	295 mm
Width	394 mm
Depth	212 mm
Net weight	9.04 kg

## Environment

IP degree of protection	IP44
-------------------------	------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>