



Example image

APPLICATION PURPOSES

- For technical building systems, industry and shipbuilding
- Exclusively for absorption of axial linear expansion during operation
- Suitable exclusively for liquid media

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- White exterior
- Bellows made of stainless steel
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating pressure	≤ 16 bar
Operating temperature	-30 – +120 °C
Product material	Non-alloy steel 1.0034 E195 (EN 10305)

Art. no.	DN	d, ø mm	D cm	La (+/-) mm	L cm	Z cm
23932	12	15	2.6	7	15.1	11.1
23933	15	18	2.6	7	14.7	10.7
23934	20	22	3.1	11	10.6	6.4
23935	25	28	3.9	13	12	7.4
23936	32	35	4.6	13	13.9	8.7

Art. no.	DN	d _ø mm	D cm	La (+/-) mm	L cm	Z cm
23937	40	42	5.9	13	14.9	8.9
23938	50	54	7	18	17.6	10.6
23939	65	76.1	8.8	22	26.2	15.6
23940	80	88.9	11.7	23	28.6	16.6
23941	100	108	14.4	23	54.2	39.2