


Doorplate CLICK SIGN A4 portrait

Article number	486737	Sales unit quantity	1 Piece
Colour	Graphite	Sales unit EAN	4005546405568
Packaging unit	1 piece	Packing weight (gross)	591 G
Base EAN	4005546405568	Country of origin	DE



Logos and awards



Product description

- CLICK SIGN doorplate range made from plastic in 5 formats
- Choice of 4 different colours to distinguish between different departments or floors
- Cardboard inserts are easy to change, simply pull out the transparent panel fully
- Suitable for large-scale applications, e.g., in training centres, hospitals, gastronomy, etc.
- With assembly set, drilling template and instructions for screwing or sticking on
- Matching PC-printable cardboard inserts sold separately
- For A4 format insert sheets (210 x 297 mm)
- Suitable printable insert labels: Article number 485602

Product features

Outer width (mm)	233
------------------	-----

Doorplate CLICK SIGN A4 portrait

Outer height (mm)	327
Outer depth / length	12 mm
Format / Format for	A4
Orientation Format	Portrait
Brand	DURABLE
Inside Label width (mm)	210
Inside Label height (mm)	297
With blank inserts	Yes
Labelling window with inserts that can be changed	Yes
Attachment type	Screw fixings
Label type	DURAPRINT®