this is proformance



TL 4000 18.0/230

LED cordless building site spotlight with tripod
18.0 V

Order no. 530375 GTIN 4030293242999

- Powerful cordless construction site light with 3 brightness settings, 1000, 2000 and 4000 lumen
- The multifunctional head can be operated as a pure work light directly with an 18 V battery. Can be used fixed with a hook or mounted on a tripod
- The lamp's three panels with two axes of rotation allow free positioning of the light angle. This allows the light to be focussed in one direction or switched to area illumination
- Ovariable-height working range of 1.1 2.2 m with tripod
- The tripod has a 1/4" connection and can also be used for other devices such as line lasers or cameras etc.
- 4 Lamp can be turned through 180°
- Multifunction control panel with LED charge level indicator, activation button, On/Off switch and USB-C charging port
- A second On/Off switch allows the light to be conveniently operated above the grip position on the tripod
- 🛟 Fast set-up and stability thanks to one-button operation and tripod stand
- The building site spotlight can also be supplied with power directly via a commercially available cold appliance connection cable (not included)
- Suitable for operation with 230 V or 110/120 V
- FLEX battery system: suitable for all FLEX 18 V battery packs. Delivery does not include battery and charger



Technical data

Battery voltage	18.0 V
Battery capacity	2.5 / 5.0 / 8.0 Ah
Voltage	230.110 V
Luminous flux	1000/2000/4000 lm
Weight without battery pack	8.2 kg

Standard equipment