

**ARCANOL-MULTITOP-1KG** [↗](#)

Bearing grease

Multi-purpose grease ARCANOL-MULTITOP

## Technical information

**Your current product variant**

Grease category	MP	Multi-purpose greases
Package size	1 KG	1 kg can

**Technical data**

$\vartheta_{O \min}$	-50 °C	Operating temperature, min.
$\vartheta_{O \max}$	140 °C	Operating temperature, max.
$\vartheta_G$	80 °C	Upper continuous limit temperature
$n \cdot d_M$	800.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Partially synthetic oil	Base oil type
$v_{40}$	82 mm <sup>2</sup> /s	Base oil viscosity at +40°C
$v_{100}$	12,5 mm <sup>2</sup> /s	Base oil viscosity at +100 °C
	2	NLGI class
	Multi-purpose grease	Grease category
$\rho$	0,87 kg/dm <sup>3</sup>	Density
	1 kg can	Container
$\approx m$	1,084 kg	Weight