



1711815-1

RJ45 Patch Cord, category 6A, 1 m, shielded, white

Body Features

Cable Color	White
Shield Style	S/FTP

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

Dimensions

Length	1.00 m 3.28 ft
Overall Outside Cable Diameter	5.588 mm 0.220 in
Wire Size (CMA)	.129 mm ² 26 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Operation/Application

Halogen Free	Yes
--------------	-----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Asia Australia/New Zealand EMEA
--------	-------------------------------------

Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6A
Cable Assembly Category	Industry Standard
Shielded	Yes

1711815-1

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant