

KEMET Part Number: PFR5221J630J11L4BULK
(F411JH221J630C)

PFR/F411, Film, Film/Foil Polypropylene, General Purpose, 220 pF, 5%, 630 VDC, 85°C, Lead Spacing = 5mm



Dimensions

L	7.2mm MAX
H	6mm MAX
T	4.5mm MAX
S	5mm -0.4mm
LL	4mm +1mm
F	0.5mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	1000

General Information

Supplier:	KEMET
Series:	PFR/F411
Dielectric:	Film/Foil Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	An Operating Temperature Up To +105C Is Allowed Under Certain Conditions. Please Consult KEMET For Details.

Specifications

Capacitance:	220 pF
Capacitance Tolerance:	5%
Voltage AC:	250 VAC
Voltage DC:	630 VDC
Temperature Range:	-55/+100°C
Rated Temperature:	85°C
Dissipation Factor:	0.04% 1kHz, 0.04% 10kHz, 0.05% 100kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	1000 V/us
Inductance:	6 nH