



Hand protection

VENICUTD07

LONG-LASTING CUT WORK

Level D cut-resistant glove, ideal for oily or aqueous environments



Specific benefits



Hygiene

· Nitrile means no risk of allergies for users



Performance

· The nitrile coating gives people working in oily/greasy environments an excellent grip on the objects they handle



Cost-effective

· User-friendly worksite package, including three pairs for weekly use

Applications

- Agriculture
- Fishing
- Public works
- Building
- Finishing works / Craftsmanship
- Maintenance

Certifications and norms



EN 388
3 X 4 2 D



ANSI/ISEA 105-2024
A4 X X

Protects against risks



Cutting



Wearing



Perforation



Hand protection

VENICUTD07

LONG-LASTING CUT WORK

Level D cut-resistant glove, ideal for oily or aqueous environments

Standards - Details



EN388:2016+A1:2018

3 [0-4] ABRASION RESISTANCE
X [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
2 [0-4] PIERCE RESISTANCE
D [A-F] CUT RESISTANCE ISO 13997

Technical details

Glove kind	Mechanical glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Weft yarn	Econocut
Coating level	Palm coated
Coating material	Nitrile
Coating finition	Grip-textured
Number of layer	Single layer
Gauge	13
Benefits element	Reach, Vendor pack
Color	Grey-Black
Size	7, 8, 9, 10
Type of packaging	Pack of 3








Safety gloves

VENICUTD07

LONG-LASTING CUT WORK

Level D cut-resistant glove, ideal for oily or aqueous environments

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
GK0407K301GR07 [VECUTD07GRG307]	Grey-Black	07	VENICUTD07	3295249214470	13295249214477	40	4	11.69 kg	30.5 cm	60.0 cm	38.5 cm
GK0407K301GR08 [VECUTD07GRG308]	Grey-Black	08	VENICUTD07	3295249214487	13295249214484	40	4	12.6 kg	61.0 cm	31.0 cm	38.5 cm
GK0407K301GR09 [VECUTD07GRG309]	Grey-Black	09	VENICUTD07	3295249214494	13295249214491	40	4	13.3 kg	30.0 cm	56.0 cm	37.0 cm
GK0407K301GR10 [VECUTD07GRG310]	Grey-Black	10	VENICUTD07	3295249214500	13295249214507	40	4	14.93 kg	30.5 cm	61.0 cm	39.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height