

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2153412124](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Red

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">215341</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Jr.-to-Pigtail
Overview	<a href="#">Off-the-Shelf Pre-Crimped Leads</a>
Product Name	Mini-Fit Jr.
UPC	193264559725

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	6.929/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire/Cable Type	UL 1015

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[215341](#) Series

**Use With**

Mini-Fit Jr. Receptacle Housing [5557](#)  
 <br>Mini-Fit BMI Slide and Lock Panel  
 Mount [44516](#) <br>Mini-Fit BMI Panel Mount  
 Receptacle Housing<br> [42474](#) , [43760](#)