



EVO103

Arctic Hood

EVO253

Arctic Hood

FEATURES

Thermally applied Reflective Tape to body & sleeves with segmented comfort trim shoulder braces.

Full length YKK® 2-way zip interactive zip fastening.

Reflective blue piping and chevron detail for enhanced night time visibility and improved modern appearance.

Double storm flap concealing a zipped pocket and pen sleeves.

Internal breast pocket & 2 internal A4 sized poachers pockets.

Underarm ventilation, chin protector & unique flip-out ID window.

Draw cord in body for optimum fit.

Neoprene inner cuff for increased comfort.

Suitable for use in the automotive industry (Car Safe).

SPECIFICATIONS

CODE: **EVO100- Yellow** **EVO250 - Orange**

SIZE OPTIONS: XS-6XL

FABRIC: EVOTECH 3 layer polyester laminate

AFTERCARE

Maximum x 25 wash cycles.

Do not wash in biological powder, wash as synthetics
 40 domestic wash only, hang dry, do not iron.

Do not tumble dry, do not dry clean, do not use bleach.

Do not use fabric softener.



STANDARDS



EN ISO 20471
 Class 3



EN343
 Class 3:3



RIS-3279 Rail Standard
 (EVO250 Only)

QUICK SIZE GUIDE (TO FIT CHEST)

| | | | | | |
|-----|-----------|-----|-----------|-----|-----------|
| XS | 31" - 34" | S | 34" - 37" | M | 37" - 40" |
| L | 40" - 43" | XL | 43" - 46" | 2XL | 46" - 50" |
| 3XL | 50" - 55" | 4XL | 55" - 59" | 5XL | 59" - 63" |
| 6XL | 63" - 66" | 7XL | 66" - 70" | | |

If the garment is being worn as a standalone garment,
 we recommend to size down one i.e. go from S to XS.