



Selection of 255 tools in foam module

CPP-255MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:53:11





DESCRIPTION



Selection of 255 tools in foam module

Selection for the agricultural or civil engineering equipment maintenance technician. Perfect for carrying out interventions on civil engineering and agricultural machines and equipment requiring large tools.

SPECIFIC DATA

Designation	PUBLIC WORKS KIT 255 TOOLS IN ABS MODULE
Sales reference	CPP-255MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France
RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-
<https://www.sam-outillage.com/>



Weight (kg)	57.000
Guarantee	O SAM TOOL guarantee.










Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

Toolset

	x 1	10-impact tool foam module M1-10MM Ref : M1-10MM
	x 1	Bodyworker's chisel 1-... Ref : 1B
	x 1	Punch 10 mm 8N-...A Ref : 8N-3A
	x 1	Constant section cape chisels 4-...-A Ref : 4-200-A
	x 1	SAMSOPPLUS® riveting hammer, three-material handle 310-...TM Ref : 310-32TM
	x 1	Mallets with interchangeable tips 320-...D Ref : 320-32D
	x 5	Long drift punches 7-...A Ref : 7-25A -- 7-35A -- 7-50A -- 7-70A -- 7-90A
	x 1	MODULOSAM® for hammers and stamping tools MOD-64
	x 1	Foam module 1/3 with 12 combination spanners 8 to 22 mm 50N-J12MM Ref : 50N-J12MM















SAM Outillage















10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France















RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



	x 12	Extra-thin combination wrench 50N-... Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 19 - 21 - 22 mm
	x 1	MODULOSAM® for combination wrenches MOD-59 Ref : MOD-59
	x 1	Foam module 1/3 with 4 pliers, polished chrome-plate P13-J4MM Ref : P13-J4MM
	x 1	Polished chrome-plated stacked-branch multigrip pliers 209-25B Ref : 209-25B
	x 1	Vice-grip, 45 - 50 mm opening 212-22 Ref : 212-22
	x 1	Polished chrome-plated universal pliers 204-...G Ref : 204-18G
	x 1	Chrome-plated polished diagonal cutting pliers 232-...G Ref : 232-16G
	x 1	Empty foam module 1/3 for 1 multigrip pliers + 1 vice-grip MOD-63
	x 1	Foam module 2/3 sawing 690-J5MM Ref : 690-J5MM
	x 1	Double tip scriber 665-1 Ref : 665-1
	x 1	Flexible rules 781-... Ref : 781-3
	x 1	Short measures with twin-material casings UB-... Ref : UB-519
	x 1	Lever type SAMSOCUT® metal saw 791 Ref : 791
	x 10	Hss bi-metal opticut metal saw blades 691-...A Ref : 691-E10A

	x 1	18 leds 180° magnetic inspection lamp 2953R Ref : 2953R
	x 1	Electrician's cable stripper knife 370-2 Ref : 370-2
	x 1	Empty foam module 1/3 for sawing accessories MODM-32 Ref : MODM-32
	x 1	Foam module 1/3 with male keys and accessories 62-R72MM Ref : 62-R72MM
	x 9	Rack of 9 hexagonal keys 62-R9A... Ref : 62-R9A
	x 9	Rack of 9 Torx® male keys 66-R9A
	x 9	Rack of 9 male 6-flat keys with spherical head in mm 67-AR9A Ref : 67-AR9A
	x 9	Rack of 9 Resistorx® male keys 59-R9A Ref : 59-R9A
	x 9	Rack of 9 long 6-flat male keys 1/4" 63-R9A... Ref : 63-R9A
	x 1	Self-retracting blade knife 378-40 Ref : 378-40
	x 1	Padlock CAD-... Ref : CAD-25
	x 1	Universal hand shears 331-16 Ref : 331-16
	x 5	Set of 5 helix pullers 761-C-5 Ref : 761-c-5
	x 1	Pen light 1396-LS Ref : 1396-LS

	x 1	1/4" socket holder EVC Ref : EVC
	x 1	Satin-finish adjustable wrenches 54-C... Ref : 54-C10
	x 1	Empty foam module 1/3 for accessories MODM-11 Ref : MODM-11
	x 1	Foam module 1/3 with 6 combination spanners 50N-J6MM Ref : 50N-J6MM
	x 6	Extra-thin combination wrench 50N-... Ref : 22 - 24 - 27 - 29 - 30 - 32 mm
	x 1	Empty foam module 1/3 for large wrenches MODM-29 Ref : MODM-29
	x 1	Foam module 1/3 with 6 tools 3/4" in mm 78-C6MM Ref : 78-C6MM
	x 1	Centre reversion 3/4" ratchet C-150
	x 1	Handle for c-150 ratchet and c-140 joint handle C-125-A
	x 1	Sliding 3/4" locking handle C-120A
	x 2	3/4" extensions C-2... Ref : C-208 - C-215
	x 1	3/4" joint C-240
	x 1	Empty foam module 1/3 for accessories 3/4" MODM-14
	x 1	Foam module 1/3 with 17 tools 3/4" 6-flat in mm 78-CH17MM Ref : 78-CH17MM



x 18

3/4" short hexagonal sockets in mm

CH-...Douilles_3/4_MM

Ref : 22 23 24 26 27 29 30 32 35 36 38 41 42 46 50 54 55mm



x 1

Empty foam module 1/3 for sockets 3/4"

MODM-15



x 1

Series S1 impact wrench 3/4"

1163

Ref : 1163



x 1

Set of 18 3/4" impact socket tools in mm

72-NC18

Ref : 72-NC18



x 16

3/4" short hexagonal impact sockets in mm

NC-...

Ref : 19 - 21 - 22 - 23 - 24 - 27 - 29 - 30 - 32 - 33 - 34 - 35 - 36 - 38 - 41 - 42 mm



x 1

3/4" impact extension

NC-2...

Ref : NC-210



x 1

3/4" impact joint

NC-240