



cubio mobile storage bench with 1 drawer-door cabinet / open cupboard / 3 drawer cabinet. Featuring a heavy duty, steel channel framework with integrated storage units 125mm diameter castors and a 40mm lino worktop. Delivered assembled. Equivalent cabinet - WxDxH:650/650/650x650x600mm. Drawer configuration: 3x 150mm, 1x 200mm with 100% extension slides (75kg U.D.L.) with single, perfo panel lined, reinforced 350 mm door and 1 adjustable height, galvanised steel shelf (100kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 2000x750x840mm.

Breite [mm]: 2000
Tiefe [mm]: 750
Höhe [mm]: 840
Bruttogewicht [kg]: 184.95
EAN-Code: 5039350086636
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Crimson red
Main RAL colour	RAL 3004
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	cubio
---------------	-------

Schubladen

Number of drawers	4
Drawer load capacity [kg]	75
Drawer height 1 [mm]	150
Drawer height 2 [mm]	150

Drawer height 3 [mm]	150
Drawer height 4 [mm]	200

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Lino
Worktop	Lino
Shelf load capacity [kg]	100
Door type	Perfo
Door height 1 [mm]	350