

PT-1830VP

Desktop P-touch Electronic Labelling System

The PT1830 has a simple to use keyboard for easy operation. This labelling machine benefits from having a large LCD display for easy viewing and editing and allows you to print bespoke labels on demand. It is supplied with a mains adaptor or can be used off site via 6 x AA batteries (not supplied)



Main Features

- 1 font style
- 9 print styles
- 4 print sizes
- Vertical printing
- 5 borders
- Up to 10mm per second print speed
- 2 print lines
- Qwerty keyboard
- 15 character x 1 line LCD screen

Consumables

- TZ TAPE 3.5mm, 6mm, 9mm, 12mm and 18mm

- 347 character memory
- Yes power adaptor
- Manual tape cutter
- 3.5mm, 6mm, 9mm,
12mm,18mm tape widths
- One year back to base warranty

PT-1830VP

Technical Specs

Font styles	1
Print styles	9
Print sizes	4
Vertical printing	Yes
Borders	5
Print speed	Up to 10mm per second
Print lines	2
Keyboard	Qwerty
LCD screen	15 character x 1 line
Character memory	347
Power adaptor	Yes
Cutter type	Manual
Tape widths	3.5mm, 6mm, 9mm, 12mm, 18mm
Warranty	1 year back to base