

Features

- LSNH Equipment Wire
- Tinned Copper Conductors

RS PRO Hook Up Wire

RS Stock No.: 0217310



Representative Image - Colour will vary

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Stranded flexible Equipment Wire designed for the internal cabling of electrical and electronic equipment. Suitable for a broad range of applications from control cabinets to specialist machine tools

Equipment wire is a flexible cable with a durable LSNH protective sheath and tinned copper conductors, available in multiple colours, ideal for colour-coding cable installations.

General Specifications

Conductor	Tinned Copper
Insulation	LSNH
Insulation Colour	Blue
Approximate Diameter	2.6 mm
Number of conductors	1
Conductor cross sectional area	1.5mm ²
Conductor construction	37 strands of 0.23mm
Length	100 MTRS

Mechanical Specifications

Minimum temperature	-40°C
Maximum temperature	+125°C

Electrical Specifications

Voltage rating	450/750V
-----------------------	----------