

KERN CKE360-3



Easy to use, self-explanatory counting scale with laboratory accuracy, ideal for the various possibilities of Industry 4.0 applications, highly accurate, counting, accuracy, counting resolution up to 360.000 points



Measuring system

Adjustment options:	External calibration
Eccentric loading at 1/3 [Max]:	10 mg
Linearity:	5 mg
Readability [d]:	1 mg
Recommended adjusting weight:	200 g (F1)
Repeatability:	1 mg
Resolution:	360000
Stabilisation time under laboratory conditions:	3 s
Tare range:	360 g
Warm up time:	2 h
Weighing capacity [Max]:	360 g
Weighing system:	Strain gauge
Weighing units:	ffa oz PCS ozt kg g lb dwt gn

Display

Display digit height (large):	2,500 cm
Display digit height (small):	2 cm

Counting

Counting resolution:	180000
Minimum piece weight at piece counting (Laboratory):	2 mg
Minimum piece weight at piece counting (Normal):	20 mg
Reference weight:	yes

Functions

Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Battery:	4x1.5 V AA
Charging time:	8 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	US UK EURO CH
Operating time:	20 h
Operating time (Backlight off):	48 h
Operating time (Backlight on):	24 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	235 x 365 x 175 mm
Net weight:	840 g
Shipping method:	Parcel service

Construction

Dimensions draft shield (ÅxH):	106 42
Dimensions housing (WxDxH):	163 x 245 x 65 mm
Level indicator:	yes
Material weighing plate:	plastic
Overall dimensions mounted (WxDxH):	163 x 245 x 123 mm
Revolving screw feet:	yes
Weighing space (ÅxH):	90 40
Weighing surface (d):	82

KERN CKE360-3



Easy to use, self-explanatory counting scale with laboratory accuracy, ideal for the various possibilities of Industry 4.0 applications, highly accurate, counting, accuracy, counting resolution up to 360.000 points

Piktogramme

STANDARD



OPTION

