



PW3 HI-VIS WORK TROUSERS

DESCRIPTION

Constructed using premium HiVisTex Pro tape and durable polyester/cotton fabric, this contemporary Hi-Vis Work Trousers provides ultimate wearer comfort. Oxford fabric reinforcement at key abrasion points and triple stitching throughout guarantees maximum durability. This trouser features top loading kneepad pockets and an easy access multiway thigh pocket for secure storage of your phone, keys and tools.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester, 600D Oxford, PU Coated, 210g**
-  **Orange/Black 28-48**

FEATURES

- Durable polycotton fabric with Texpel stain resistant finish
- Texpel™ Stain Eco a premium stain resistant finish to repel grime and water
- High rise back waistband ensures protection in all working positions
- Easy access cargo pocket
- Extendable leg length (31" to 33")
- Free pair of kneepads included with this trouser
- Triple-stitched seams for extra durability
- 2 Side pockets
- Two back patch pockets
- Double rule pocket
- D-ring for keys or ID cards
- Hammer loop for secure storage of work tools

STANDARDS

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)
ANSI/ISEA 107 SUPPLEMENTAL CLASS E

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
PW340OBR	ORANGE/BLACK	28-14

FEATURES



TOP-LOADING KNEE PAD POCKETS
Top-loading knee pad pockets for quick and easy access



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



HEAT APPLIED SEGMENTED REFLECTIVE TAPE
This symbol indicates that the garment has heat applied reflective tape



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends
sports and lifestyle trends with function,
a modern fit and improved comfort.

GET THE
COLLECTION



TECHINCAL INFORMATION



SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777) Bracetown
Business Park Clonée Dublin 15 D15 YN2P, Ireland
Cert No: 2777/14048-03/E00-00

· Wash garment inside out and fully
fastened

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
PW340OBR28	Orange/Black	65	45	36	.960	5850.000	5036108303953	15036108793133
PW340OBR30	Orange/Black	65	45	36	.960	5850.000	5036108303960	15036108793140
PW340OBR32	Orange/Black	65	45	36	.998	5850.000	5036108303977	15036108793157
PW340OBR33	Orange/Black	65	45	36	1.016	5850.000	5036108303984	15036108793164
PW340OBR34	Orange/Black	65	45	36	1.028	5850.000	5036108303991	15036108793171
PW340OBR36	Orange/Black	65	45	36	1.044	5850.000	5036108304004	15036108793188
PW340OBR38	Orange/Black	65	45	36	1.066	5850.000	5036108304011	15036108793195
PW340OBR40	Orange/Black	65	45	36	1.060	5850.000	5036108304028	15036108793201
PW340OBR41	Orange/Black	65	45	36	1.080	5850.000	5036108304035	15036108793218
PW340OBR42	Orange/Black	65	45	36	1.100	5850.000	5036108304042	15036108793225
PW340OBR44	Orange/Black	65	45	36	1.080	5850.000	5036108304059	15036108793232
PW340OBR46	Orange/Black	65	45	36	1.120	5850.000	5036108304066	15036108793249
PW340OBR48	Orange/Black	65	45	36	1.140	5850.000	5036108304073	15036108793256