



verso kitted cupboard with vertical partition. Featuring a robust, fully welded steel housing with a central vertical partition and double, reinforced doors with 4 adjustable height, galvanised steel shelves (75kg U.D.L.) and 4x 100mm, 4x 175mm drawers with 100% extension slides (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 1050x550x2000mm.

Breite [mm]: 1050  
Tiefe [mm]: 550  
Höhe [mm]: 2000  
Bruttogewicht [kg]: 155.20  
EAN-Code: 5039350115084  
Zolltarifnummer UK: 94032080  
Ursprungsland: GB

## Produkteigenschaften

|                      |               |
|----------------------|---------------|
| Product surface      | Powder coated |
| Product material     | Sheet steel   |
| Main colour          | Crimson red   |
| Main RAL colour      | RAL 3004      |
| Secondary colour     | Light grey    |
| Secondary RAL colour | RAL 7035      |

## Artikelbeschreibungen

|               |       |
|---------------|-------|
| Product brand | verso |
|---------------|-------|

## Schubladen

|                           |     |
|---------------------------|-----|
| Number of drawers         | 8   |
| Drawer load capacity [kg] | 75  |
| Drawer height 1 [mm]      | 100 |
| Drawer height 2 [mm]      | 100 |
| Drawer height 3 [mm]      | 100 |

|                      |     |
|----------------------|-----|
| Drawer height 4 [mm] | 100 |
| Drawer height 5 [mm] | 175 |
| Drawer height 6 [mm] | 175 |
| Drawer height 7 [mm] | 175 |
| Drawer height 8 [mm] | 175 |

## Schrank, Gehäuse, Werkbank und EAP

|                          |       |
|--------------------------|-------|
| Shelf load capacity [kg] | 75    |
| Door type                | Plain |
| Door height 1 [mm]       | 1925  |