

PRODUCT DATA SHEET

CORDLESS LED LAMPS

PRODUCT CODE	EAN CODE	PACK QTY	LENGTH
BL30	7314150164349	1	351 mm
BL60	7314150164356	1	395 mm
BL80	7314150164363	1	437 mm

PRODUCT KEY FEATURES:

- Durable and strong with a triple layer construction (polycarbonate tube, ABS inner sleeve, TP rubber outer sleeve) in oil and chemical resistant material
- Temperature resistant
- A high intensity and pure white and very bright light for work in all types of conditions. Very high visibility with true colour recognition
- Long operating time: 4 hours (BL30 & BL60) and 3.5 hours (BL80)
- Rechargeable: battery type: Ni-MH
- Using advanced technology with a controlled microprocessor and an "intelligent" charger
- Short charging time: 1.5 hours
- Charger: Input: 100-240V AC. Output: 12V DC, 500mA
- Equipped with a bendable swivel hook
- LUX output: BL30: 1,200 LUX / BL60: 1,700 LUX / BL80: 2,000 LUX
- IP Rating : 54

