

Overlight OL

Overlight OL 254 is suitable for use with moving machinery giving asymmetric lighting with minimal shadow. (Flicker free tubes ensure that rotating objects will not appear to be stationary, a common optical effect when standard fluorescent tubes are used.) Silver grey anodized aluminium frame with an anti-dazzle screen. Angle continuously adjustable. With own switch and 3 m cable. The lighting units are isolated from the workbench.

Name	Width mm	Lamp power	Suitable for	Code	Code RS Components
Overlight OL254	1200	54 W	all benches	OL254	1357323

Overlights can be mounted on all lamp mounts produced by Treston (WB: support bracket HSB, / Concept, TP and Workshop: light and balancer rail, / TPH: tool and lighting support KT).

