



### Main

Range of product	Mureva Styl
Product or component type	Cable entry
Range compatibility	Mureva Styl
Quantity per set	Set of 10

### Complementary

Number of cables	3
Cable entry	Easy valve access
Condition of use	Indoor/outdoor
Material	SEBS PP (polypropylene)
Colour tint	White (RAL 9003)
Length	49 mm
Height	8 mm
Width	42 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Quality labels	AENOR NF
IP degree of protection	IP55
IK degree of protection	IK08

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations