

# VARTA Recharge Accu Recycled AA 2100 mAh Blister 4



The most eco-friendly product line with 25% recycled battery content.



## Information

- Contains 25% recycled materials per battery
- Pre-charged and with 'ready to use' technology - for immediate usage straight from the pack
- Rechargeable hundreds of times without memory effect
- Suitable for all standard and smart devices of daily use and all NiMH chargers
- Best use in high drain applications and devices with constant energy requirements like LED flashlights, GPS systems, wireless mice and more
- Lasts up to 8 times longer in digital cameras\*
- \* vs. VARTA Energy. Based on IEC 60086-2 (ed. 14.0) HDA-Test (high drain application). May vary by device.

## Article Details

Ordernumber	56816 101 404
Customs Tariff Number	85075000
Country Of Origin	China
IEC	HR6
Others	AA, Stilo
Nominal Capacity	2100 mAh
Voltage	1.20
System	Nickel Hydride
Consumer Unit	4
DG Profile	NiMH battery UN3496 (sea to 100kg ok)

## Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 931583	80.00	16.00	120.00	0.13
SK2 (Inner carton 2)						
SK1 (Inner carton 1)	10	40 08496 931590	89.00	126.00	83.00	1.32
VSK (Master carton)	100	40 08496 931606	135.00	425.00	183.00	13.29
PAL (Pallet)	7800	40 08496 931613	800.00	1,200.00	1,248.00	1,057.46
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
6	13		78		10	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany  
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

