

Datasheet



rotary pump

SRL 980, approx. 30 l/min

Item number: 13 055
EAN: 4103810130557
Discount group: A

technical data

application: for filling measuring vessels, storage cans and canisters

application: container, for 60 / 200 / 220 l

Pumping media: For oils, up to SAE 90, self-lubricating, non-aggressive media, fuel oil, diesel, petroleum

delivery capacity (l/rotation): approx. 0,25

Materials of parts in contact with liquid

seals: NBR

discharge: Steel discharge spout

Pump housing: cast iron GG 25

colour: Pantone 294c, blue satin

length suction tube: 980

barrel screw coupling: G 2" male

Weight (kg): 4,9

specification

- with suction filter
- easy to operate hand-rotating operation for an easy use
- Through barrel screw coupling height adjustable
- Packed in carton box
- With bar code

packaging

Dimensions LxWxH (mm): 350 x 160 x 120

weight including package (kg): 5,2

Packing unit: 1.0