

Chainsaw XGT®

UC014G

40Vmax • 0 - 24,7 m/s • 30 cm / 12"

Efficient brushless saw with a high chain speed for heavy-duty use with tool-less chain adjustment.

XGT® 40Vmax battery powered chainsaw. A very high powered chainsaw made for professionals. equivalent to 42 mL class engine chain saw. Tool-less chain adjustment makes the saw even more convenient. This chainsaw is perfect for construction sites, gardens or summer cottages.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	25,5 m/s
chain bar length	300 mm (12")
Chain Pitch	0,325 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	51
Chain Oil Tank	260 ml
Brushless Motor	✓
Vibration Level, Cutting Wood	5,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Pressure Level (L _{pA})	94 dB(A)
Sound Power Level (L _{WA})	102 dB(A)

User benefits

- Lightweight for reduced operator fatigue
- Large oil filling port with view window allows operator to easily add and check bar oil level
- Main power switch with auto power-off function for battery saving and avoiding unintentional start up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Adjustable automatic chain lubrication with large oil reservoir

Link to product - www.makitauk.com



Related products

Optional AC

191T86-6

Guide Bar 12" / 30cm, 1.1mm



191T90-5

Saw chain 80TXL, 12" / 30 cm, 1,1



419288-5

Chain Protection Cover 14" / 35 cm



782023-7

Wrench 13 -16



Other

User manual

Parts drawing