



Part Number : 1301030064

Product Description : Watertite Wet Location Incandescent Hand Lamp Only, 100W with TEFLON Globe

Series Number : 130103

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1220



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp Only, 100W with TEFLON Globe
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps
UPC	78678861330

Agency

CSA	LR85374
UL	E59251

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	127.00mm (5.000")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	254.00mm (10.000")
Lamp Type	A21
Length	N/A
Material - Globe	PTFE
Material - Guard	N/A
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Mar 27, 2025