

OLS-C05, G 1/2", Opened in media (SPST n.c.), circular connector M12x1, 4-pin

OLS-C05, G 1/2", Opened in media (SPST n.c.), circular connector
M12x1, 4-pin

Item number: 14241092

Quantity: 1 pcs.

Order code: OLS-C05-G1Z-HNCM4-ZZZZZ-ZZZ W101OLS5Z1LH

Overview: OLS-C05, G 1/2", Opened in media (SPST n.c.), circular connector M12x1, 4-pin
Optoelectronic level switch, High temperature version
Model: OLS-C05
Process connection: G 1/2"
Output Signal: one switching output (PNP)
Switch function: Opened in media (SPST n.c.)
Power supply: 12 - 32 V DC
Electrical connection: circular connector M12x1, 4-pin
pin assignment el. connection: 1=U+, 3=U-, 4=SP
Operating pressure: max. 25 bar
Permissible medium temperature: -40...170 °C
Wetted parts: Stainless steel 1.4571, borosilicate glass, epoxide resin
Specifications according to data sheet: LM 31.33

Details: OLS-C05, G 1/2", Opened in media (SPST n.c.), circular connector M12x1, 4-pin
Optoelectronic level switch, High temperature version
Model: OLS-C05
Process connection: G 1/2"
Output Signal: one switching output (PNP)
Switch function: Opened in media (SPST n.c.)
Power supply: 12 - 32 V DC
Electrical connection: circular connector M12x1, 4-pin
pin assignment el. connection: 1=U+, 3=U-, 4=SP
Operating pressure: max. 25 bar
Permissible medium temperature: -40...170 °C
Wetted parts: Stainless steel 1.4571, borosilicate glass, epoxide resin
Specifications according to data sheet: LM 31.33