

Eaton EBH213TTV1

Catalog Number: EBH213TTV1

Eaton Bussmann series low voltage NH fuse base, Switch disconnecter, low voltage, 400 A, AC 690 V, NH2, AC23B, 3P, IEC, 60mm busbar, top cable terminals, for connection of sector shaped conductors, V-clamps



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH fuse base	EBH213TTV1
	EAN
	5027590409223
Product Length/Depth	Product Height
215 mm	330 mm
Product Width	Product Weight
190 mm	4326 g
Compliances	Certifications
CE	IEC/EN 60947-1
	IEC 60947-3

Product specifications

Type

Fuse accessory

Application

Motor control centres, distribution boards, Cable distribution cabinets

Amperage Rating

400 A

Rated operational power at AC-23A, 400 V, 50 Hz

0.16 kW

Rated permanent current (Iu)

400 A

Rated uninterrupted current (Iu)

400 A

Conditioned rated short-circuit current Iq

0.08 kA

With error protection

No

Number of poles

Three-pole

Rated operation power at AC-23, 400 V

0.16 kW

Rated short-time withstand current (Icw)

80 A

Electrical connection type of main circuit

Cable clamp

Actuator position

Front side

Actuator type

Cover grip

Construction size

NH2

Fuse shape

Horizontal

Suitable for

Busbar mounting

Resources

Catalogs

CA134002EN

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Declarations of conformity

UKCA fuse switch disconnectors, EBC, EBV and EBH series

CE fuse switch disconnectors, EBC, EBV and EBH series

Technical data sheets

10275 EBV Vertical fuse switch-disconnector

Technical service bulletins

10293 EBH Horizontal switch-disconnector

NH2

Suitable for fuses

NH2

Cable entry type

Other

Mounting method

60 mm busbar mounting

100 mm busbar mounting

Mounting plate

Voltage rating

690

Degree of protection (front side)

IP30

Electrical connection type

Cable clamp

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia