

## Datasheet

### 3way Iso AA converter 0-10/0-10V 24V

RS Stock number 794-8546



#### Microcompact Analogue/Analogue Converters

DIN rail mounting Microcompact analogue/analogue converters for industrial applications.

3-way isolation

LED indicator

Screw/spring terminals

IP 20 protection

Input Range	0 → 10 V
Input Type	Analogue
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-25°C
Mounting Type	DIN Rail
Operating Temperature Range	-25 → +60 °C
Output Range	0 → 10 V
Output Type	Analogue
Signal Conditioner Type	Isolation
Supply Voltage	16.8 → 30 V dc, 19.2 → 28.8 V ac