

## 28 LM

### 4-way wheel wrench

Truck

Code **6228770** ETIM **EC003993**

EAN **4010886622872** UNSPSC **27-11-17-14**

Country of origin **Germany** eCl@ss **21-04-01-90**

Customs tariff number  
**82041100**



### Article description

- Acc. to DIN 3119, ISO 6788
- For trucks, agricultural machines, tractors and industrial uses
- Vanadium steel 31CrV3
- Grey powder-coated
- Hot forged hexagon
- The collar, typical of GEDORE 4-way wheel wrenches, enlarges the welding area
- The positive-fit joint remains solid even under extreme loading
- Dimensions: 750 x 750 mm

### Article parts list

24x27x30x32

### Article information

Contents [Qty of pieces]	<b>1</b>	Insert-Ø 1	<b>34,5 mm</b>
Net weight [kg]	<b>5,555 kg</b>	Insert-Ø 2	<b>38,5 mm</b>
Total length [mm]	<b>750 mm</b>	Width across flats [mm]	<b>24 x 27 x 30 x 32</b>
Total width [mm]	<b>750 mm</b>	Width across flats 2 [mm]	<b>27</b>
Total height [mm]	<b>46 mm</b>	Width Across Flat 3 [mm]	<b>30</b>
Surface	<b>grey powder-coated</b>	Width Across Flat 4 [mm]	<b>32</b>
Use	<b>For trucks, agricultural machines, tractors and industrial uses</b>	Insert-Ø 3	<b>42,0 mm</b>
Material	<b>31CrV3</b>	Insert-Ø 4	<b>45,0 mm</b>
Width across flats 1 [mm]	<b>24</b>	Insert-Ø	<b>34,5 mm x 38,5 mm x 42,0 mm x 45,0 mm</b>