

50

Carpenters' Pincers

DIN ISO 9243



50 00 210



50 01 225



- for heaviest duty
- specially favoured by craftsmen for their precise workmanship
- extreme wear resistance and well balanced
- cutting edges additionally hardened; cutting edge hardness approx. 60 HRC
- Special tool steel, forged, oil-hardened



Article No.	EAN 4003773-	↔ mm		Pliers	Head	Handles	Cutting capacities Ø mm	g
50 00 130	014423	130					1,6	135
50 00 160	013129	160					1,8	215
50 00 180	013136	180					2,0	303
50 00 210	013143	210	✔	black atramentized	polished		2,2	398
50 00 225	013150	225					2,2	427
50 00 250	013167	250					2,2	563
50 00 300	015710	300					2,4	862
50 01 130	015789	130					1,6	141
50 01 160	015802	160					1,8	223
50 01 180	016021	180					2,0	316
50 01 210	016052	210	✔	black atramentized	polished	plastic coated	2,2	411
50 01 225	016083	225					2,2	437
50 01 250	016267	250					2,2	583
50 01 300	016915	300					2,4	903

51

Hammerhead Style Carpenters' Pincers

DIN ISO 9243



51 01 210



- with striking face for driving in nails
- cutting edges additionally hardened; cutting edge hardness approx. 60 HRC
- Special tool steel, forged, oil-hardened



Multi-functional: driving in and pulling nails

Article No.	EAN 4003773-	↔ mm		Pliers	Head	Handles	g
51 01 210	023104	210	✔	black atramentized	polished	plastic coated	413