

HexArmor SharpsMaster 7082

Seamless High Visibility Needlestick Technology

Key Features

Highest needlestick resistance on the market

Highest level of cut resistance on palm and palm side of fingers: exceeds EN388 Cut Level 5

Durable and long lasting

Nitrile coating for superior grip and liquid resistance

Attributes

Glove type:

Reusable

Offers protection from:

Puncture

Working Environments

Indoor

Wet

Dry

Clean

Level of grip

Low

Level of Dexterity

Medium

Special Features

Latex Free



European Standards

EN388

Resistance to Mechanical hazards

Commonly used in:

Waste Management

Medical/Vet/Dental

Local Authority

Emergency Services

Product Support

Contact Customer Services

020 8443 9000

customer.services@polyco.co.uk

Technical support

020 8443 9090

technical@polyco.co.uk

Specifications

	7	8	9	10	11	EN388
HexArmor SharpsMaster 7082	HEX7082/S	HEX7082/M	HEX7082/L	HEX7082/XL	HEX7082/XXL	4542