

## 248 H-100

### Recoilless hammer

Code	ETIM
8728570	EC000161
EAN	UNSPSC
4010883872850	27-11-16-02
Country of origin	eCl@ss
Austria	21-04-09-00
Customs tariff number	
39269097	



### Article description

- With hickory handle
- Splinter-proof, shatter-proof and wear-resistant polyamide heads, 75 Shore D, tested to -20° C
- Powder-coated with silver hammer-effect enamel

### Article information

Contents (Qty of pieces)	1	Surface	powder-coated
Version/Execution	Splinter-proof, shatter-proof and wear-resistant polyamide heads, 75 Shore D, tested to -20° C	Material	Polyamide (PA)
Net weight [kg]	6,935 kg	Diameter of head 1	100 mm
Total length [mm]	1.050 mm	Shaft material	Hickory
Total width [mm]	210 mm	Magnet	no
Total height [mm]	101 mm	Hardness [Shore-D]	75 Shore-D